


# Gold Oboe Cable Kit (EtherCAT and CAN)



## Notice

This guide is delivered subject to the following conditions and restrictions:

- This guide contains proprietary information belonging to Elmo Motion Control Ltd. Such information is supplied solely for the purpose of assisting users of the Gold Oboe servo drive in its installation.
- The text and graphics included in this manual are for the purpose of illustration and reference only. The specifications on which they are based are subject to change without notice.
- Information in this document is subject to change without notice.

Document no. MAN-G-OBOE-CBLKIT (Ver. 1.000)

Copyright © 2015

Elmo Motion Control Ltd.

All rights reserved.

## Catalog Number

CBL-GDCTROKIT

## Revision History

Version	Date	Details
Ver. 1.000	December 2015	Initial release



**Chapter 1: Introduction .....4**  
    1.1. Cable Kit (CBL-GDCTROKIT) ..... 4

**Chapter 2: Port A Cable .....5**

**Chapter 3: Port B Cable .....7**

**Chapter 4: Port C Cable .....9**

**Chapter 5: I/O Cable.....11**

**Chapter 6: 24 VDC Auxiliary Supply.....13**

**Chapter 7: CAN Terminator .....14**



## Chapter 1: Introduction

This document provides the wiring details for the cables used to connect Elmo's Gold Oboe servo drive with the end-user application. The servo drive-side pinouts are provided in the *Gold Oboe Installation Guide*.

The cables come in one length: 2 meters (6 ½ feet).

### 1.1. Cable Kit (CBL-GDCTROKIT)

**NOTE:**

It should be noted that this kit does not include any CAT5E RJ-45 for EtherCAT/CAN and Mini-USB communication cables. Please purchase these cables separately. These items are standard cables that can be purchased locally.

This cable kit includes the following cables:

Function	Description
Port A	15-Pin D Type Male Connector
Port B	9-Pin D Type Male Connector
Port C	15-Pin High Density D Type Male Connector
I/O cable	15-Pin High Density D-Type Female Connector
24 VDC auxiliary supply	2-Pin Phoenix Plug-in Connector




## Chapter 2: Port A Cable


The Port A cable is a 6-pair 24-AWG shielded twisted-pair cable. It is connected using a D-type 15-pin male connector to the Gold Oboe Port A D-sub connector.

The cable is open on the feedback side so that it can be connected to the motor-feedback connector.


The general pinout of the Port A cable is as follows:

Pin No.	Signal	Color	Twisted & Shielded Wire	Plug
1	HC	Green	Twisted Pair 1	 MALE <b>15-Pin D Type Male Connector</b>
10	HB	Yellow		
3	COMRET	White	Twisted Pair 2	
4	+5V	Brown		
5	PortA_ENC_A-	Orange	Twisted Pair 3	
6	PortA_ENC_A+	Cyan		
7	PortA_ENC_INDEX-	Blue	Twisted Pair 4	
8	PortA_ENC_INDEX+	Red		
2	HA	Pink	Twisted Pair 5	
9	COMRET	Gray		
14	PortA_ENC_B-	Black	Twisted Pair 6	
15	PortA_ENC_B+	Purple		
11	COMRET	-	Drain Wire	

### Pin Positions



**15-Pin D-Type Female Connector**



**15-Pin D-Type Male Connector**



**Note:** The specific functionality of each pin is described fully in the *Gold Oboe Installation Guide*.



**Figure 1: Feedback Port A Cable**




## Chapter 3: Port B Cable


The Port B cable is a 4-pair 24-AWG shielded twisted-pair cable. It is connected using a D-type 9-pin male connector to the Gold Oboe Port B D-sub connector.

The cable is open on the feedback side so that it can be connected to the motor feedback connector.

The general pinout of the Port B cable is as follows:


Pin No.	Signal	Color	Twisted & Shielded Wire	Plug
1	PortB_ENC_A+/SIN+	Brown	Twisted Pair 1	 <p><b>9-Pin D Type Male Connector</b></p>
6	PortB_ENC_A-/SIN-	White		
3	PortB_ENC_INDEX+	Red	Twisted Pair 2	
8	PortB_ENC_INDEX-	Blue		
5	COMRET	Gray	Twisted Pair 3	
4	+5V	Pink		
7	PortB_ENC_B-/COS-	Green	Twisted Pair 4	
2	PortB_ENC_B+/COS+	Yellow		
9	COMRET	-	Drain Wire	

### Pin Positions



G-OBOE056A-B

**9-Pin D-Type Female Connector**



**9-Pin D-Type Male Connector**



**Note:** The specific functionality of each pin is described fully in the *Gold Oboe Installation Guide*.



**Figure 2: Feedback Port B Cable**






## Chapter 4: Port C Cable

The Port C cable is an 8-pair 24-AWG shielded twisted-pair cable. It is connected using a D-type 15-pin high density male connector to the Gold Oboe Port C D-sub connector.

The cable is open on the user interface side so that it can be connected to the controller interface connector.


The general pinout of the Port C cable is as follows:

Pin No.	Signal	Color	Twisted & Shielded Wire	Plug
1	PortC_ENCO_A+	Cyan	Twisted Pair 1	 <p><b>15-Pin High Density D Type Male Connector</b></p>
2	PortC_ENCO_A-	Orange		
3	PortC_ENCO_B+	Purple	Twisted Pair 2	
4	PortC_ENCO_B-	Black		
5	PortC_ENCO_Index+	Red	Twisted Pair 3	
10	PortC_ENCO_Index-	Blue		
7	STO_RET	Gray	Twisted Pair 4	
6	STO1	Pink		
11	STO2	White/Yellow	Twisted Pair 5	
12	STO_RET	White/Green		
9	COMRET	Green	Twisted Pair 6	
13	ANARET	Yellow		
15	ANALOG1+	White/Red	Twisted Pair 7	
14	ANALOG1-	White/Black		
8	Reserved	Brown	Twisted Pair 8	
-	N/C	White		
*	PE	-	Drain Wire	

\* - Connector 15 Pin Male Frame




### Pin Positions



G-OBOE056A-C

15-Pin High Density D-Type Female Connector



CEL0040A-DWG  
CEL0008A

15-Pin High Density  
D-Type Male Connector

**Note:** The specific functionality of each pin is described fully in the *Gold Oboe Installation Guide*.



Figure 3: Port C Cable




## Chapter 5: I/O Cable


The I/O cable is an 8-pair 24-AWG double shielded twisted-pair cable. It is connected using a D-type 15-pin female connector to the Gold Oboe on the servo drive side.

The cable is open on the end side so that it can be connected to the controller interface connector.

The general pinout of the I/O cable is as follows:

Pin No.	Signal	Color	Twisted & Shielded Wire	Plug
1	IN1	Orange	Twisted Pair 1	 <p><b>15-Pin High Density D-Type Female Connector</b></p>
2	IN2	Cyan		
3	OUT1	Blue	Twisted Pair 2	
4	OUT2	Red		
5	OUT3	Yellow	Twisted Pair 3	
13	OUT4	Green		
7	IN	Purple	Twisted Pair 4	
8	IN4	Black		
9	VDDRET	White	Twisted Pair 5	
10	VDD	Brown		
11	IN5	Gray	Twisted Pair 6	
12	IN6	Pink		
14	VDDRET	White/Black	Twisted Pair 7	
15	VDD	White/Red		
6	INRET1-6	White/Yellow		
*	PE	-	Drain Wire	

\* - Connector 15 Pin High Density Frame



**Note:** The specific functionality of each pin is described fully in the *Gold Oboe Installation Guide*.



Figure 4: I/O Cable




## Chapter 6: 24 VDC Auxiliary Supply

The 24 VDC auxiliary supply is a single twisted-pair 24-AWG double-shielded cable. It is connected to the auxiliary power supply connector.

The cable is open on the end side so that it can be connected to the auxiliary power supply.

The general pinout of the 24 VDC auxiliary supply is as follows:



**Note:** The specific functionality of each pin is described fully in the *Gold Oboe Installation Guide*.



Figure 4: 24 VDC Auxiliary Supply Cable




## *Chapter 7: CAN Terminator*

The CAN terminator is used only for CAN applications. It is used to terminate the CAN communication line.

The CAN terminations prevent the CAN signal reflection at the end of the physical lines.

The reflection suppresses the CAN signal which may lead to Error Frames and causes the CAN controller message to be discarded. **120 Ohm resistors** are required on both physical ends of the CAN network to prevent the signal reflection.



120  $\Omega$  Resistor  
assembly inside



## Inspiring Motion

*Since 1988*

For a list of Elmo's branches, and your local area office, refer to the Elmo site [www.elmomc.com](http://www.elmomc.com)

